

Technical data sheet

IGP-DURA®*xal*/ 4201E-L3

Deep matte, highly weather-resistant powder coating for high-quality façades and design objects with the appearance of anodized aluminum.



Characteristics

- Deep matte
- Smooth finish
- Pearl mica, Premium
- Super durable facade quality,
3 years Florida > 50% residual gloss
- Lower cure
- Touchproof



Material approvals

- [Qualicoat Nr. P-2055, class 2](#)
- [AAMA 2604-13, independent test report](#)
- [EPD IGP-DURA®*xal* 42](#)
- [Qualicoat Nr. P-1909, class 2](#)



Powder properties

Particle size:	< 100 µm
Solids:	> 99 %
Density:	1.3 kg/l-1.6 kg/l
Suitability for storage:	min. 18 months at ≤ 25 °C in an unopened original container
Color tones:	RAL Metallic and individual metallic colors on request



Processing

Pre-treatment

The substrate must be free from oil, grease and oxidation products. The pretreatment depends on the type of substrate and the corrosion protection to be achieved. We recommend the following pretreatments:

Aluminium

- Chromating according to DIN EN 12487
- Pre-anodization
- Chrome-free pretreatment according to GSB International and QUALICOAT specifications

Steel

- Zinc phosphating

Galvanised steel

- Zinc phosphating
- Chrome (III) passivation
- Chromating according to DIN EN 12487

For improved corrosion protection for applications on steel / galvanised steel, the use of corrosion protection primer IGP-KORROPRIMER 10 or IGP-KORROPRIMER 60 is recommended.

The suitability of the pretreatment method used is generally to be tested by the coater in advance with appropriate test methods. The minimum requirement for aluminium substrates / galvanised steel components is to carry out a boiling water test with a subsequent cross-cut adhesion and tape test. We refer to the guidelines of the GSB International, Qualicoat and Qualisteelcoat certifications. For further information: see also our special leaflet on pre-treatment (IGP-TI 100).

Coating devices

All conventional electrostatic systems with corona charging.


For the construction and operation of powder coating plants, the following regulations must be complied with: ATEX RL 2014/34/EU, EN 50177, DIN EN 16985.

Recommended film thickness

60 µm - 80 µm

To achieve a uniform finish with textured coatings, or where there are colour- or product-specific differences in hiding power, higher film thicknesses may be required. The relevant processing guidelines must be followed. To estimate the quantity of powder coating required in advance, the necessary Film thickness must be determined on a product-by-product basis.

Curing conditions



T Object	t min	t max
180 °C	20 minutes	25 minutes
190 °C	10 minutes	15 minutes
200 °C	6 minutes	10 minutes

In order to determine ideal curing conditions, we recommend practical trials with the respective object and curing oven.

Additional information regarding processing can also be found in the IGP processing instruction VR207.2 "IGP-DURA®*xal*". Our Technical Customer Service Department will be happy to help you.

Application

For optimum coating and surface quality, please follow the recommendations in the processing guideline VR207.2. For effect powders, please also note the effect category on the container label.

Reclaimability

To prevent colour variations caused by loss of effect during coating, pearlescent mica products should be processed without reclaiming.

In the case of automated coating with an appropriate batch size, a certain quantity of reclaimed powder may be added, depending on the shade's categorisation.

Please refer to the effect category on the container label and processing guideline VR207.2.



Film properties

Tested on

Substrate:	Aluminum (AlMg1), 0.8 mm chrom-free
Film thickness:	60 µm - 80 µm
Object temperature:	190 °C, 10 min.

Appearance

Gloss level	3-11 R'/60°	DIN EN ISO 2813 2015-02
-------------	-------------	-------------------------

Mechanical tests

Cross-cut adhesion test	Gt 0	DIN EN ISO 2409 2020-12
Mandrel bending test / Tape test	≤ 5 mm	DIN EN ISO 1519 2011
Impact test / Tape test	≥ 2.5 Nm	ASTM D 2794 1993
Erichsen cupping / Tape test	≥ 5 mm	DIN EN ISO 1520 2007-11

Weathering tests

3 years Florida, 5° south	> 50 % residual gloss	DIN EN ISO 2810 2021-01
Xenon-arc lamps, 1000h, 90%	> 90 % residual gloss	DIN EN ISO 16474-2 2014-03

Corrosion tests

Condensation water test, 1000h	No infiltration, no blisters	DIN EN ISO 6270-2 2018-04
Acetic acid salt spray test, 1000h	No infiltration, no blisters	DIN EN ISO 9227 2017-07

Chemical tests

Mortar resistance	Easily removable after 24h with no residues.	ASTM D 3260 2001
-------------------	--	------------------



Further information

Packaging

20 kg cardboard box with inserted antistatic PE liner
300 kg Big Bag

Overcoating suitability

Preliminary tests are mandatory for overcoating painted surfaces.

Printing and glueing

Preliminary tests are mandatory for printing and glueing of painted surfaces.

Protection of coated parts

Coated parts should be packed after cooling with suitable materials without plasticizers. They should be stored protected from the weather to avoid the formation of condensation and thus water spots on the coating.

Cleaning

The coated parts must be cleaned according to the directives RAL-GZ 632 or SZFF 61.01. Technical Information IGP-TI 106 must also be observed when dealing with pearl mica effects.

Paint removal and disposal

After use, coated goods should be supplied to the normal recycling process. The disposal methods for sludges or residual powders must be observed in accordance with the local official provisions whilst taking Waste Code "080201 Coating Powder Wastes" in accordance with the European Waste Catalogue into consideration.

This application-related advice is given to the best of our knowledge. However, this information is non-obligatory and does not exempt you from carrying out your own tests. Application, use and processing of these products are beyond our control and are therefore on your responsibility.

Consult the Safety Data Sheet prior to use. Article-specific safety data sheet and comprehensive risk management measures available at: [igp-powder.com](https://www.igp-powder.com)